


STANDARD SUBDRAIN OUTLET


TYPE A

For existing subdrain pipes 12" or less in diameter. (5)



PRESSURE RELEASE OUTLET TYPE B

- 1) Perforated Subdrain (Polyethylene Corrugated Tubing).
- 2 Removable Rodent Guard (Appropriately sized to fit pipe).
- (3) If corrugated metal pipe is used, an outlet 2" larger than existing subdrain pipe is required. If double-walled PE or PVC pipe is used, an outlet pipe of the same diameter as the existing subdrain pipe may be used.
- (4) The pipes should be coupled in one of the two following ways: (1) Use an inside fit reducer coupler (coupler must be inserted a minimum of 12" into C.M.P.); or (2) Insert 12" of the existing subdrain pipe into the corrugated metal outlet pipe, then fully seal the entire opening with grout.
- (5) For existing subdrain pipes larger than 12" in diameter, use Special Outlet, Type C.



Possible Contract Item: Subdrain Outlet, (RF-19F) Possible Tabulation: 104-5C



SUBDRAIN OUTLETS
(STANDARD SUBDRAIN,
PRESSURE RELEASE AND SPECIAL)